

Power Pedestals

- For indoor and outdoor use
- Quick and easy installation
- Available in a variety of heights, colors and configurations



BRINGING POWER BEYOND THE WALL!

An ideal solution for...

- Commercial Buildings
- Campuses
- Airports & Transit Hubs
- Campgrounds
- Public Parks
- ...and more



Durable Construction for Indoor and Outdoor Use

- Available in Brushed Stainless Steel, Powder Coated Bronze, or Powder Coated Black with added UV and scratch protection
- Welded construction from heavy gauge 304 Stainless Steel to withstand the harshest environments

Installation Options

SURFACE MOUNT

(BASE VARIES DEPENDING ON HINGE STYLE)



DIRECT BURY



- Pre-installed grounding hardwire and stainless steel anchoring hardware for concrete included
- Pre-drilled holes for easy mounting to the ground surface
- Flush hinge versions are ideal for areas with limited space such as in front of a wall and include internal mounting bracket to save space

- No need to wait for concrete pour/set
- Removeable access panel on side eases wiring device installation



Proudly
Made in the USA



UL Listed in
USA & Canada



ADA Compliant
Heights



NEMA 3R Rated
Indoor/Outdoor



Lockable
Covers

Available with Leviton Electrical Wiring Devices

- Weather- and Tamper-Resistant USB Receptacle with Type A and C ports to meet any charge requirements



- Designed to satisfy current UL standards for auto-monitoring, our Weather- and Tamper-Resistant Self-Test GFCIs periodically conduct automatic internal tests to confirm that they can respond to a ground fault

- Can accommodate any standard decorator style electrical wiring device

Hinged Top Versions


- **Control Access** - Durable stainless steel cover is equipped with a locking tab to prevent unauthorized use and to ensure important cords are not unplugged
- **24/7 Protection** - Spacing between cover and pedestal to allow wiring to pass through while-in-use
- **Weather-Resistant** - Self-closing cover prevents ingress of water from outdoor elements

Weatherproof While-In-Use Cover Versions

- Complies with the National Electric Code® (2020) Section 406.9 for weatherproof enclosures in damp and wet locations



Ordering Information



| Pedestal Style | Gang | Installation Type | Height (in.) | Includes Receptacles | STAINLESS STEEL Cat. No. | BLACK Cat. No. | BRONZE Cat. No. |
|----------------|--------|-------------------|----------------------------------|----------------------|-----------------------------|-------------------|--------------------|
| Standard Hinge | 1-Gang | Direct Bury | 18" once installed; 42" total | Yes* | 1BH42-1S | 1BH42-1E | 1BH42-1Z |
| | | | | No | 1BH42-S | 1BH42-E | 1BH42-Z |
| | | Surface Mount | 18" | Yes* | 1PH18-1S | 1PH18-1E | 1PH18-1Z |
| | | | | No | 1PH18-S | 1PH18-E | 1PH18-Z |
| | 24" | Yes* | 1PH24-1S | 1PH24-1E | 1PH24-1Z | | |
| | | No | 1PH24-S | 1PH24-E | 1PH24-Z | | |
| | 2-Gang | Surface Mount | 18" | Yes** | 2PH18-2S | 2PH18-2E | 2PH18-2Z |
| | | | | No | 2PH18-S | 2PH18-E | 2PH18-Z |
| Flush Hinge | 1-Gang | Surface Mount | 18" | Yes* | 1PF18-1S | 1PF18-1E | 1PF18-1Z |
| | | | | No | 1PF18-S | 1PF18-E | 1PF18-Z |
| | | | 24" | Yes* | 1PF24-1S | 1PF24-1E | 1PF24-1Z |
| | | | | No | 1PF24-S | 1PF24-E | 1PF24-Z |
| No Hinge | 1-Gang | Surface Mount | 18" | Yes*** | 1PS18-3S | 1PS18-3E | 1PS18-3Z |
| | | | | No | 1PS18-S | 1PS18-E | 1PS18-Z |
| | | | 24" | Yes*** | 1PS24-3S | 1PS24-3E | 1PS24-3Z |
| | | | | No | 1PS24-S | 1PS24-E | 1PS24-Z |

In addition to the above offering, our power pedestals are available in gray, green, brown and other custom colors with additional lead times. Contact your local Leviton specialist for more information.

NOTES: *Comes with 20 Amp Weather- and Tamper-Resistant GFCI (G5362-WTW)
 **Comes with 20 Amp Weather- and Tamper-Resistant GFCI (G5362-WTW) and 20 Amp Weather- and Tamper-Resistant Type A and C USB Receptacle (W5833-W)
 ***Comes with 20 Amp Weather- and Tamper-Resistant GFCI (G5362-WTW) and Weatherproof While-In-Use Cover (IUM1V-GY)



Visit our Website at:
www.leviton.com/powerpedestals
 email: commercial@leviton.com

Q-1483A

061523

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2023 Leviton Manufacturing Co., Inc. All rights reserved.